



QuickTask™ 0500/0550 Flat Mop Head

Polyester / Cellulose Blend Flat Mop Head

Description

The QuickTask range consists of a variety of flat mop heads that can be easily attached to a choice of flat mop head frame and handle assemblies. The flat mop heads are compatible with the QuickTask hinged mop frames 2749 (stainless steel) and 2740 (autoclavable polypropylene).

The QuickTask TASK0500/TASK0550 mop heads are constructed from a hydroentangled polyester / cellulose blend fabric with a synthetic fiberfill core. This provides a highly sorbent mop head which is suitable for the removal of light soild, residues and biofilms. Designed for single use, the mop heads are compatible with a wide range of chemicals and disinfectants.

The TASK0550 is provide sterile by gamma irradiation at no less than 25 kGy.

Technical Data

Mop head component materials (cleaning surface first)	Nonwoven polyester / cellulose cover; Synthetic fiberfill core	
Construction	Multi-layer sewn lamination	
Dimensions; inches (cm)	5 x 15 (39 x 13)	
Attribute; (units)	Value **	Test Method
Mop weight, dry; (g/mop)	31	Contec Method
Sorbency, IPA/water, (mL/mop)	293	CTM005
Non-volatile residue, NVR		IEST-RP-CC004.2, Sec. 6.1.2
In deionised water; (g/m ²)	0.015	
In isopropanol; (g/m ²)	0.007	
Particles ≥ 0.5µm; (x10 ⁶ /mop)	24.8	IEST-RP-CC004.2, Sec. 5.2
Fibers > 100µm; (Fibers/mop)	116.0	IEST-RP-CC004.2, Sec. 5.2

** ND = None detected; levels are below detection limit of test equipment

Part Number	Description	Packaging
TASK0500	QuickTask polyester/cellulose flat mop head	4 Each/Bag, 12 Bags/Case
TASK0550	QuickTask polyester/cellulose flat mop head, sterile	1 Each/ Double Bag, 40 Bags/Case

Notes:

- 1) The information presented here is applicable to the part numbers shown above, as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.
- 2) Data shown are typical values and should not be used as product specifications.
- 3) Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- 4) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Revision date: 11/26/12



North America
P.O. Box 530
Spartanburg, SC 29304 USA
Phone: +1-864-503-8333
www.contecinc.com

Europe
ZI du Prat – RP 3707
56037 VANNES Cedex
FRANCE
+33 297 437 690

China
No.17 Longyun Road
Suzhou 215024
CHINA
+ 86-512-6274 4050